

The perfect solution for

- Civil Defence/Fire Brigades
- Hospitals
- Nuclear Industry
- Pharmaceutical Industry

RadEye G20-10 / G20-ER10

X-ray and gamma survey meters for ambient equivalent dose and dose rate measurement

Features of RadEye G20-10/G20-ER10

- Fast response even below 1 $\mu\text{Sv/h}$
- Light weight (300 g), excellent grip with and without gloves
- Rugged and compact design, thick rubber protective cover
- Low cost of ownership with > 500 h operation time with 2 AAA batteries – rechargeable NiMH-cells can be used
- Menu-driven user interface results in low training cost and immediate familiarity
- Huge internal data memory for both scaler results and continuous data recording
- Bright backlit LCD display – plain text messages - different languages can be selected
- Audible indication: single pulse or chirper mode proportional to count rate
- Earphone output for operation in loud environment
- Designed to meet and exceed IEC 60846-1




RadEye G20-10: 4250687

RadEye G20-ER10: 425068710

The RadEye G20-10 and G20-ER10 are excellent gamma survey meters with a flat energy response curve from 17 keV to 1.3 MeV according to ambient equivalent dose $H^*(10)$. The RadEye G20-ER10 model covers the whole dose rate range from background to 100 mSv/h.

The instrument is part of the growing RadEye family of high-end stand-alone meters, which are designed to meet the most demanding user expectations.

**RadEye G20-10 and RadEye G20-ER10
Relative Gamma Response for H*(10)**



Accessories

Gamma test-adaptor for RadEye G20-10/G20-ER10 (50 g Lu₂O₃): Order Number: 4254948

62 mm diameter, 7 mm height (aluminium housing)

55 mm diameter, 3 mm height (Lu₂O₃ ceramics)

Induced net dose rate for RadEye G20: 0.25 µSv/h (25 µrem/h).

Time requirement for response verification approx. 5 min.



Car Adapter Interface Order number: 425067065

- AAA NiMH cells can be charged in the instrument
- Continuous monitoring in the car / fire truck with lit backlight of the display
- RS 232 / USB / Bluetooth communication options



Inductive RadEye charger Order number: 425067080

In conjunction with the special battery lid (**Order number: 425067034**) and 2 standard NiMH AAA-cells, the inductive RadEye charger allows permanent operation of a RadEye G20-10 or RadEye G20-ER10.

The RadEye remains galvanically isolated from the external DC-supply.



Special battery lid



Inductive charger

Detector	Pan cake GM with multi-element energy filter
Measuring Range (RadEye G20-10)	0.01 µSv/h – 2 mSv/h
Measuring Range (RadEye G20-ER10)	0.01 µSv/h – 100 mSv/h
Energy Range (ambient equivalent dose rate)	17 keV – 1.3 MeV (± 20%)
Response	approx. 4 cps / µSv/h (every meter is individually calibrated)
Linearity	- 9% to +11%
Temperature Range	-20°C - +50°C

This specification sheet is for informational purposes only and is subject to change without notice. Thermo Fisher Scientific makes no warranties, expressed or implied, in this product summary.
© 2007 Thermo Fisher Scientific Inc. All rights reserved. LITRadEyeG20-10_G20-ER10-e-V1.3_14Nov07

www.thermo.com

Thermo
SCIENTIFIC

USA:
27 Forge Parkway
Franklin MA 02038
USA
+1 (800) 274-4212
+1 (508) 520 2815 fax

UK:
Bath Road
Beenham, Reading RG7 5PR
England
+44 (0) 118 971 2121
+44 (0) 118 971 2835 fax

Germany/International:
Frauenauracher Straße 96
D 91056 Erlangen
Germany
+49 (0) 9131 909-0
+49 (0) 9131 909-205 fax